

Hei-VAP Core

Overview

Ventilation cap with PTFE inlet and free of ground joints. Optionally available with replenishment valve

Clear digital display for monitoring the current values and separate button to display the set values

IP 42

Two separate operating knobs for adjusting the rotation speed and heating temperature with LED ring light system for activity indication

Available as hand or motor lift

Activated lock feature prevents inadvertent adjustments.

Residual heat indicator when $> 50^{\circ}\text{C}$

Standby button stops all functions and lifts the evaporator flask out of the heating bath on motor lift models


Equipped with proven smart details such as Easy Clip, patented clamping sleeve, lift stop to limit immersion depth, universal 5-L-heating bath, various glass accessories etc.

Using an optional cable extension, the operating panel can be detached for use outside closed fume hoods

Ergonomically optimized heating bath handles sit securely in your hand



MADE IN
GERMANY

 heidolph

 heidolph
research made easy